


ALLURAVISION™ DEEP 74" ELECTRIC FIREPLACE




Specifications

Model	BTU	Width		Height		Depth		Viewing Area (H x W)
		Actual	Framing	Actual	Framing	Actual	Framing	
NEFL74CHD-1	5000 / 9000	76 3/4"	74 13/16"	17 5/16"	16 1/8"	5 13/16"	6 1/16"	11 1/16" x 72 1/2"

Dimensions



Label Location



W415-2879 / 03.20.20

ALLURAVISION™ DEEP 74" ELECTRIC FIREPLACE




Clearances


Minimum Mantel Clearances

⚠ WARNING

- When using paint or lacquer to finish the mantel, the paint or lacquer must be heat resistant to prevent discolouration.





Side View (Wall Mount)



Side View (recessed into a wall)

Framing



Measurements from body of appliance:	
Sides, Back, Top	0"

Product information provided is not complete and is subject to change without notice. Please consult the installation manual for the most up to date installation information.

W415-2879 / 03.20.20

Wolf Steel Ltd., 24 Napoleon Rd., Barrie, ON L4M 0G8 Canada • 1(866)820-8686 • www.napoleon.com


APPAREIL ÉLECTRIQUE ALLURAVISION^{MD} PROFONDE 74"




Spécifications

Modèle	BTU	Largeur		Hauteur		Profondeur		Dimensions de Vision (H x L)
		Réel	Ossature	Réel	Ossature	Réel	Ossature	
NEFL74CHD-1	5000 / 9000	76 3/4	74 13/16	17 5/16	16 1/8	5 13/16	6 1/16	11 1/16 x 72 1/2

Dimensions



Emplacement des Étiquettes





W415-2879 / 03.20.20


Dégagements Dégagements Minimum à la Tablette

⚠ AVERTISSEMENT

- Lorsque vous utilisez de la peinture ou de la laque pour finir la tablette, la peinture ou la laque doit être résistante à la chaleur pour éviter la décoloration.



Ossature



L'information du produit fourni n'est pas complète et est sujet de changer sans préavis. Consultez le manuel d'installation pour information d'installation actuel.

W415-2879 / 03.20.20